

Datasheet

AHSA1 monoclonal antibody (M02), clone 4F3-B6

Gene Alias: AHA1, C14orf3, p38

Catalog Number: H00010598-M02

Regulation Status: For research use only (RUO)

Product Description: Mouse monoclonal antibody
raised against a full-length recombinant AHSA1.

Clone Name: 4F3-B6

Immunogen: AHSA1 (AAH00321, 1 a.a. ~ 338 a.a)
full-length recombinant protein with GST tag. MW of the
GST tag alone is 26 KDa.

Sequence:

MAKWGECDPRWIVEERANATNVNWHWTERDASN
WSTDKLKTLFLAVQVQNEEGKCEVTEVSKLDGEASIN
NRKGKLIFFYEWSVKLNWTGTSKSGVQYKGVHVEIPNL
SGENSVDEVEISVSLAKDEPDNLVALMKEEGVKLLRE
AMGIYISTLKTEFTQGMILPTMNGESVDPVGPALKTE
ERKAKPAPSKTQARPVGKIPKTKITLKETFLTSPPELY
RVFTTQELVQAFTHAPATLEADRGKGFHMVDGNVSG
EFTDLVPEKHIVMKWRFKSWPEGHFATITLTFIDKNGE
TELCMEGRGIPAPEEERTRQGWQRYFEGIKQTFGY
GARLF

Host: Mouse

Reactivity: Human

Applications: ELISA, IP, S-ELISA, WB-Re, WB-Tr
(See our web site product page for detailed applications
information)

Protocols: See our web site at
<http://www.abnova.com/support/protocols.asp> or product
page for detailed protocols

Isotype: IgG1 Kappa

Storage Buffer: In 1x PBS, pH 7.4

Storage Instruction: Store at -20°C or lower. Aliquot to
avoid repeated freezing and thawing.

Entrez GeneID: 10598

Gene Symbol: AHSA1