



Extremely comfortable and precise dispensing pump Programmable on pump module or via control module

Calibration for exact dispensing Flexible, thanks to replaceable single and multichannel pump heads

rotarus® volume

rotarus® volume 100		Order No. 950 15 62	
Characteristics		Interfaces	
Flow rate range	0.0036 - 5400 ml/min		RS232 interfaces
Depending on the pump head used*			USB interface
Changeable pump heads	Yes		Analog input for speed specifi cation
Channels	1 - 12		Analog output for speed
	(Depending on the pump head type used)		Digital input Start/Stop; rotation direction
Range of speed	5 – 500 1/min		Selectable digital output
Operation	TFT touchscreen	General data	
External control module	Yes	Housing	White powder coated
Program memory	20	Continuous mode	Yes
Pump direction change	Yes	Motor capacity	85 Watt
Calibration function	Yes	Motor type	DC Motor
Speed control	Load-independent	Max. power consumption	150 VA
Speed configuration TFT touchscreen	TFT touchscreen	Power supply	100-240 VAC ; 50-60 Hz
Speed configuration (increments) 1/min	0.1	Protection class	IP54
Operation modes		Standards	CE
	Pumps according to speed	Depth/width/height in mm	270/100/220
	Pumps according to flow rate	Weight	10.1 kg
	Dispensing according to volume		
·	Dispensing according to time		

*Indicated flow rates are approximate values measured with water, at (0 meters suction lift and free outlet.
--	--

Dispensing according to volume in time

Cycle dispensing

Cycle time specification

Tube leakage monitoring
Blockage detection
Pump head detection
Tube detection
Stackable
Usable on stand
Drop-free dispensing
System assignment
Soft start

Tube service life monitoring

Configurable via menu



Special functions